





# Connector Comparison Sheet

	Old Connector 3190-650 EZ-400-TM	New Connector 3190-2533 EZ-400-TM-X																																								
<b>1. Materials&amp;Plating</b>	<table border="1"> <thead> <tr> <th></th> <th><u>Material</u></th> <th><u>Plating</u></th> <th><u>Thickness</u></th> </tr> </thead> <tbody> <tr> <td>1) Body</td> <td>Brass</td> <td>Nickel</td> <td></td> </tr> <tr> <td>2) Center Contact</td> <td>Beryllium Copper</td> <td>Silver</td> <td></td> </tr> <tr> <td>3) Coupling nut</td> <td>Brass</td> <td>Nickel</td> <td></td> </tr> <tr> <td>4) Ferruel</td> <td>Copper</td> <td>Nickel</td> <td></td> </tr> </tbody> </table>		<u>Material</u>	<u>Plating</u>	<u>Thickness</u>	1) Body	Brass	Nickel		2) Center Contact	Beryllium Copper	Silver		3) Coupling nut	Brass	Nickel		4) Ferruel	Copper	Nickel		<table border="1"> <thead> <tr> <th></th> <th><u>Material</u></th> <th><u>Plating</u></th> <th><u>Thickness</u></th> </tr> </thead> <tbody> <tr> <td>1) Body</td> <td>Brass</td> <td>Albaloy</td> <td></td> </tr> <tr> <td>2) Center Contact</td> <td>Beryllium Copper</td> <td>Gold</td> <td></td> </tr> <tr> <td>3) Coupling nut</td> <td>Brass</td> <td>Albaloy</td> <td></td> </tr> <tr> <td>4) Ferruel</td> <td>Copper</td> <td>Albaloy</td> <td></td> </tr> </tbody> </table>		<u>Material</u>	<u>Plating</u>	<u>Thickness</u>	1) Body	Brass	Albaloy		2) Center Contact	Beryllium Copper	Gold		3) Coupling nut	Brass	Albaloy		4) Ferruel	Copper	Albaloy	
	<u>Material</u>	<u>Plating</u>	<u>Thickness</u>																																							
1) Body	Brass	Nickel																																								
2) Center Contact	Beryllium Copper	Silver																																								
3) Coupling nut	Brass	Nickel																																								
4) Ferruel	Copper	Nickel																																								
	<u>Material</u>	<u>Plating</u>	<u>Thickness</u>																																							
1) Body	Brass	Albaloy																																								
2) Center Contact	Beryllium Copper	Gold																																								
3) Coupling nut	Brass	Albaloy																																								
4) Ferruel	Copper	Albaloy																																								
<b>2. Dimension&amp;Outline</b>																																										
<b>3. Installation</b>	Need Braid Trim	No Braid Trim																																								

## 4. Test Curve



\* The test curve is based on the assembly 1m cable with 2 connectors on each end.